

표준 JMQSS 부속품

Alloy/ANSI 칼라 코드	6" 길이 모델 번호	12" 길이 모델 번호	대응 커넥터 모델 번호	케이블 클램프 모델 번호	안전 클립 모델 번호
Iron-Constantan 304 SS Sheath J	SICSS-010(*)-6 SICSS-020(*)-6 SICSS-032(*)-6 JMQSS-040(*)-6 JMQSS-062(*)-6 JMQSS-125(*)-6	SICSS-010(*)-12 SICSS-020(*)-12 SICSS-032(*)-12 JMQSS-040(*)-12 JMQSS-062(*)-12 JMQSS-125(*)-12	SMPW-J-F		
CHROMEGA™ -ALOMEGA™ 304 SS Sheath K	SCASS-010(*)-6 SCASS-020(*)-6 SCASS-032(*)-6 KMQSS-040(*)-6 KMQSS-062(*)-6 KMQSS-125(*)-6	SCASS-010(*)-12 SCASS-020(*)-12 SCASS-032(*)-12 KMQSS-040(*)-12 KMQSS-062(*)-12 KMQSS-125(*)-12	SMPW-K-F		
CHROMEGA™-ALOMEGA™ Super OMEGACLAD™ XL Sheath K	SCAXL-010(*)-6 SCAXL-020(*)-6 SCAXL-032(*)-6 KMQXL-040(*)-6 KMQXL-062(*)-6 KMQXL-125(*)-6	SCAXL-010(*)-12 SCAXL-020(*)-12 SCAXL-032(*)-12 KMQXL-040(*)-12 KMQXL-062(*)-12 KMQXL-125(*)-12	SMPW-K-F		
OMEGA-P™-OMEGA-N™ Super OMEGACLAD™ XL Sheath N	SNNXL-020(*)-6 SNNXL-032(*)-6 NMQXL-040(*)-6 NMQXL-062(*)-6 NMQXL-125(*)-6	SNNXL-020(*)-12 SNNXL-032(*)-12 NMQXL-040(*)-12 NMQXL-062(*)-12 NMQXL-125(*)-12	SMPW-N-F	PCLM-SMP	SMCL
CHROMEGA™-Constantan 304 SS Sheath E	SCXSS-010(*)-6 SCXSS-020(*)-6 SCXSS-032(*)-6 EMQSS-040(*)-6 EMQSS-062(*)-6 EMQSS-125(*)-6	SCXSS-010(*)-12 SCXSS-020(*)-12 SCXSS-032(*)-12 EMQSS-040(*)-12 EMQSS-062(*)-12 EMQSS-125(*)-12	SMPW-E-F		
Copper-Constantan 304 SS Sheath T	SCPSS-020(*)-6 SCPSS-032(*)-6 TMQSS-040(*)-6 TMQSS-062(*)-6 TMQSS-125(*)-6	SCPSS-020(*)-12 SCPSS-032(*)-12 TMQSS-040(*)-12 TMQSS-062(*)-12 TMQSS-125(*)-12	SMPW-T-F		
OMEGALLOY™ Inconel 600 Sheath N	SNNIN-010(*)-6 SNNIN-020(*)-6 SNNIN-032(*)-6 NMQIN-040(*)-6 NMQIN-062(*)-6 NMQIN-125(*)-6	SNNIN-010(*)-12 SNNIN-020(*)-12 SNNIN-032(*)-12 NMQIN-040(*)-12 NMQIN-062(*)-12 NMQIN-125(*)-12	SMPW-N-F		

모든 부속품은 별매품입니다.

*접지를 선택하십시오.

E(노출, Exposed), G(접지, Grounded), U(비접지, Ungrounded)

주문 예: KMQSS-125G-6,
초소형 간편 연결 프로브, K형, 0.125" OD 스테인리스 스틸 보호관,
길이 6", 접지 접점
KMQSS-M300U-300, 초소형 간편 연결 프로브, K형, 스테인리스
스틸 보호관, 3 mm OD, 길이 300mm, 비접지 접점.